UNIT CLOSED CIRCUIT COOLER

MODEL # ATWB 24-6N24 SCALE NTS


EVAPCO, INC. Evapco


DWG. # WB3242412-DRD-ST REV. SERIAL # DATE 11/7/2025


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]

## **FACE C**







SHIPPING WEIGHT 85940 lbs+ [38985] kg+ OPERATING WEIGHT

130200 lbs+ [59060] kg+

HEAVIEST SECTION WEIGHT

18690 lbs+ [8480] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR