UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 20-5M24-Z

EVAPCO, INC. Evapco



DWG. # REV. WB36M2410-DRC-SF DATE 9/18/2025 SERIAL #

DRAWN BY:


NO. OF SHIPPING SECTIONS

NOTES:


SHIPPING

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE
- FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]



FACE A




OPERATING

WEIGHT

101200 lbs+ [45905] kg+

65900 lbs+ [29895] kg+



13770 lbs+ [6250] kg+

HEAVIEST SECTION

WEIGHT