UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 7-3J12 NOTES: 1. (M)- FAN MOTOR LOCATION

EVAPCO, INC. evapco




REV. CW4C071206-DRA-ST


SERIAL #


DWG. #

DATE_{10/29/2025}

- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]







SHIPPING 9270 lbs+ [4205] kg+ WEIGHT

OPERATING WEIGHT

12760 lbs+ [5790] kg+

HEAVIEST SECTION WEIGHT

7370 lbs+ [3345] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

TAM