UNIT CLOSED CIRCUIT COOLER		EVADOO T	N.C. PYCI	oco Di	wg. # CW4C071806-DRA-ST	REV.
MODEL # ATWB 7-3H18	SCALE NTS	EVAPCO, I	NC.	SE	ERIAL #	DATE 11/2/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING S 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDI GVD DENOTES GROOVED FLG DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DR. 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kI 6. *-APPROXIMATE DIMENSIONS DO NO FOR PRE-FABRICATION OF CONNECT PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. R RECOMMENDED STEEL SUPPORT DR 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	AWINGS) Pa] T USE FING	FACE PLAN VIE		ACCESS DOOR	CE C ACCESS I	FACE D
1'-9 3/8" 1'-7 1/2" * (2) 4" [100] BFW 2" [50] MPT MAKE-UP 2" [50] MPT DRAIN 1'-11 1/8" [587] 3" - 51/4" [107] 5'-3 5/8" [1616] 7'-4" [2235	FLUID IN FLUID OUT	2'-11 3/8" [899] 1'-10 7/8" * 4'-7/8" [1241] 12'-1/2" [3670] 51/4" * [1530] 1'-3" [80] MPT OVERFLOW		18	2'-0" 486]	
SHIPPING 13970 lbs+ [6340] kg	g+	OPERATING 19260 lbs+ [8740] kg+	HEAVIEST SECTION WEIGHT	10950 lbs+ [4970] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: TAM