UNIT CLOSED CIRCUIT COOLER	EVADCO	TNC (eyglogo)	DWG. # WV050908-DRC-ST	REV.
MODEL # LRWB 5-4J9 SCALE	EVAPCO,	INC. Evapeo	SERIAL #	DATE 11/5/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWING 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLIS [METRI 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTI 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX	TO G H FT IN C] [mm] FACE R 5'-5/8"	FACE C		FACE D
2'-6 3/8" * -		15'-2 1/4" [4629] FACE A	6'-3" [1905]	1
4" [100] BFW FLUID IN 4" [100] BFW FLUID OUT	2'-3" [1297] [686] * 7'-31/4" [2216]	1/2" [15] FPT VENT		6'-7 3/4" [2026]
3 1/4" TYP. = 3" [80] MPT OVERFLOW	2 5/8" L 8 3/4" [67] [222]	ACCESS DOOR 8'-5 3/8" [2575]	1" [25] MPT MAKE-UP	1'-8 1/8" [511]
2" [50] MPT 1'-8 [53] DRAIN 5'-5/8" [1540] FACE B	- 4 7/8" 7/8" - 1'-1 5/8" [346]	15'-2 1/4" 15'-2 1/4" FACE A	•	DOOR
SHIPPING 5720 lbs+ [2595] kg+	OPERATING 9350 lbs+ [4245] kg+	HEAVIEST SECTION 5720 lbs+ [2595] kg+	NO. OF SHIPPING SECTIONS 1	RAWN BY: TLS