				Taura "	155.
UNIT CLOSED CIRCUIT COOLER	EVAPCO,	TNC	evapco	DWG. # WV080908-DRE-SF	REV.
MODEL # LRWB 8-4L9-Z SCALE NTS	LVAPCO	T14C.		SERIAL #	DATE 11/4/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm] 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING. 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 8. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS	FACE B [7] PLAN VIEW	10" 1	FACE	-2 1/4" -4629]	FACE D
2'-1/2" *	2'-3" * [1392] 686] * [7'-7" [2311] 	3.7/8"	(2) 1/2" [15] FPT VENT SERIES FLOW PIPING (BY OTHERS) AUX. CROSSOVER DRAIN (BY OTHERS) ACCESS DOOR 8'-5 3/8" [2575]	6'-3" [1905] 1'-8 1/8" [511] -2" [50] MPT MAKE-UP	6'-7 3/4" [2026] — ACCESS DOOR

HEAVIEST SECTION WEIGHT

8600 lbs+ [3905] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

SHIPPING WEIGHT OPERATING WEIGHT

13650 lbs+ [6195] kg+

8600 lbs+ [3905] kg+