UNIT CLOSED CIRCUIT COOLED					0	DWG. # WAY (2004 A P.P.F. G.F.		REV.
MODEL #	CLOSED CIRCUIT COC	CCALE	EVAPCO,	TNC	evapco		WV080910-DRE-SF	-
MODEL #	LRWB 8-5M9-Z	SCALE NTS		11401		SERIAL #		DATE 11/3/2025
2. MPT FPT I BFW GVD FLG PE D 3. +UNI ACCI 4. 3/4" [ RECG 5. DIME 6. * - AF USE CON 7. MAKI 20 ps 8. SERI	S: FAN MOTOR LOCATION DENOTES MALE PIPE THREA DENOTES FEMALE PIPE THREA DENOTES FEMALE PIPE THREA DENOTES BEVELED FOR WE DENOTES GROOVED DENOTES FLANGE DENOTES PLAIN END IT WEIGHT DOES NOT INCLUE ESSORIES (SEE ACCESSORY 19mm] DIA. MOUNTING HOLE COMMENDED STEEL SUPPORT ENSIONS LISTED AS FOLLOWS PPROXIMATE DIMENSIONS DOE FOR PRE-FABRICATION OF INECTING PIPING. (E-UP WATER PRESSURE SI [137 kPa] MIN, 50 psi [344 kPa LIES FLOW PIPING AND AUX. C LIN ARE BY OTHERS	READ ELDING  DE / DRAWINGS) ES. REFER TO T DRAWING /S: ENGLISH FT IN [METRIC] [mm] O NOT	FACE B PLAN VIEW	7'-10"	FACE	<b>C</b>		FACE D
2	2'-1/2" * <del>-</del>   3'-8 ;	.7/8" * <del>-</del>			FACE	-2 1/4" 4629 ] E <b>A</b>	-	
(2) 4" [	[100] BFW FLUID IN		5'-2 1/4"		(2) 1/2" [15] FPT VENT SERIES FLOW PIPING	_	[ 6'-3" ]	
	F[100] BFW FLUID OUT		2'-10 1/2" * [ 1583 ] 8'-2 1/2" [ 2502 ]		(BY OTHERS)  AUX. CROSSOVER DRAIN (BY OTHERS)	<u></u>		6'-7 3/4" [ 2026 ]
	[80] MPT	M <sub>0</sub>	2 5/8" 1 8 3/4"		ACCESS DOOR 8'-5 3/8" [ 2575 ]		1'-8 1/8"	ACCESS
		4 1/4" -   -10" [ 864 ]   CE B		1'-3 7/8"		-2 1/4" 4629 ]	2" [50] MPT MAKE-UP	DOOR

HEAVIEST SECTION WEIGHT

10010 lbs+ [4545] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

SHIPPING WEIGHT OPERATING WEIGHT

15450 lbs+ [7010] kg+

10010 lbs+ [4545] kg+