UNIT CLOSED CIRCUIT COOLER		EVADO	O TNC	evapco	DWG. # WLEP81814-DRD-SF	REV.	
MODEL #	LSWE 8P-7O18-Z	SCALE NTS	EVAPO	CO, INC.		SERIAL #	DATE <sub>12/14/2025</sub>
2. MPT D FPT DE BFW D GVD D FLG DI PE DEI 3. +UNIT ACCES 4. 3/4" [19 RECON 5. DIMEN 6. * - APF USE FO 7. HEAVII 8. MAKE 20 psi [ 9. SERIE:	AN MOTOR LOCATION JENOTES MALE PIPE THREAD ENOTES FEMALE PIPE THREAD ENOTES BEVELED FOR WELE JENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUDE SSORIES (SEE ACCESSORY D JENOTES FLANGE MMENDED STEEL SUPPORT D JESIONS LISTED AS FOLLOWS: PROXIMATE DIMENSIONS DO N OR PRE-FABRICATION OF COI EST SECTION IS COIL SECTION UP WATER PRESSURE [137 kPa] MIN, 50 psi [344 kPa] S FLOW PIPING AND AUX. CRO LARE BY OTHERS	AD DING  E RAWINGS) REFER TO DRAWING ENGLISH FT IN [METRIC] [mm] NOT NNECTING PIPIN DN MAX	F <u>AC</u> PLAN VIE	: 2300 3		18'-0" [ 5486 ]	<u>FACE D</u>
	2'-1/2" *	+	3'-8 7/8" * [ 1140 ]		<u>FACE</u>	<u>E A</u>	
3'- [ 5 1/8" *	SERIES FLOW — PIPING (BY OTHERS)  (2) ACCESS DOOR — 3" [80] MPT — OVERFLOW  2'-11 7/8" [911]  3'-2 5/8" — [981]  3'-8 3/8" — [1127]	7'-1( 238	2" [50] MPT	6'-1/2" [1842] 13'-3 7/8" [4061] 7'-3 3/8" [2219]	(4) 1/2" [15] FPT VENT  AUX. CROSSOVER DRAIN (BY OTHERS)	18'-0" [ 5486 ]	
FACE B							
SHIPPING WEIGHT	22800 lbs+ [10345]		PERATING 33530 lbs+ [152 VEIGHT	10] kg+ HEAVIEST S WEIG		NO. OF SHIPPING SECTIONS 2	DRAWN BY: