NIT CLOSED CIRCUIT COOLER		DOLER				DWG. # WB3243608-DRC-SF	REV.
10DEL #	ATWB 24-4M36-Z	SCALE NTS	EVAPCO,	INC.		SERIAL #	DATE _{11/10/2025}
2. HEAVI 3. MPT D FPT DI BFW C GVD C FLG D PE DE 4. +UNIT ACCES 5. MAKE- 20 psi 6. *-APPF FOR P PIPINC 7. SERIE DRAIN 8. 3/4" [19] RECOI 9. DIMEN	AN MOTOR LOCATION EST SECTION IS UPPER S ENOTES MALE PIPE THR ENOTES FEMALE PIPE TH ENOTES BEVELED FOR N ENOTES GROOVED ENOTES PLAINE NOTES PLAIN END WEIGHT DOES NOT INCLE SCORIES (SEE ACCESSO) UP WATER PRESSURE MIN [137 kPa], 50 psi MAX ROXIMATE DIMENSIONS E RE-FABRICATION OF CONS S FLOW PIPING AND AUX BY OTHERS. BMMJ DIA. MOUNTING HOI MMENDED STEEL SUPPO SIONS LISTED AS FOLLO NGLISH FT-IN IETRIC [MM]	EAD IREAD WELDING UDE RY DRAWINGS) [344 kPa] SO NOT USE NECTING . CROSSOVER LES, REFER TO RT DRAWING.		FACE B AN VIEW		FACE C (4) ACCESS DOOR	.
						FACE A	
			[178]	1'-3 1/4"			
FL	(100) BFW UID IN 3/4" *	- 5'-9 1/4" * [1759] *	3'-3/8" * [924] * 9'-1/8" [2748]	(16) 1/2" [15] FPT VENT	60 60	M M	
½ 2'-1 1/4" [643]			6" * AU 8'-2 1/4" 2494]	SERIES FLOW PIPING (SEE NOTE 7) X. CROSSOVER DRAIN (SEE NOTE 7)			
1'-5" [433] 3	(4) 2" [50] MPT (4) 3" [80] MAKE-UF (4) 3" [80] MPT (5) 1, [13]	T	4'-8" [1422]		1'-11 1/8" [587]	1'-11 1/8 [587]	3"

FACE B

FACE A