UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 24-7P36-Z

EVAPCO, INC. Evapco



DWG. # REV. WB3243614-DRC-SF DATE<sub>12/13/2025</sub> SERIAL #

## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

139600 lbs+ [63325] kg+


WEIGHT

WEIGHT

9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [MM]



30830 lbs+ [13985] kg+



WEIGHT

211200 lbs+ [95800] kg+