UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 24-4N40-Z

EVAPCO, INC. Evapco



DWG. # REV. WB3244008-DRC-SF DATE_{12/15/2025} SERIAL #


NOTES:

SHIPPING

WEIGHT


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE
- 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [MM]





FACE A

NO. OF SHIPPING SECTIONS



169040 lbs+ [76680] kg+

HEAVIEST SECTION

WEIGHT

21840 lbs+ [9910] kg+

OPERATING

WEIGHT

105500 lbs+ [47855] kg+