


| | | |
|---------|-----------------------|-----------|
| UNIT | CLOSED CIRCUIT COOLER | |
| MODEL # | ATWB 10-3K18-Z | SCALE NTS |

| | | |
|----------|------------------|----------------|
| DWG. # | WB3TM1806-DRC-SF | REV. - |
| SERIAL # | | DATE 1/11/2026 |

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
4. FPT DENOTES FEMALE PIPE THREAD
5. BFW DENOTES BEVELED FOR WELDING
6. GVD DENOTES GROOVED
7. FLG DENOTES FLANGE
8. PE DENOTES PLAIN END
9. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
10. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
11. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
12. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
13. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
14. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN
METRIC [mm]




FACE B

PLAN VIEW

FACE C



FACE D



FACE A