UNIT CLOSED CIRCUIT COOLER

MODEL # ATWB 20-6M12-Z SCALE NTS


EVAPCO, INC. Evapeo

DWG. # WB36M1212-DRC-SF REV. SERIAL # DATE_11/14/2025


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]





FACE A





SHIPPING WEIGHT 36500 lbs+ [16560] kg+ OPERATING WEIGHT

55460 lbs+ [25160] kg+

HEAVIEST SECTION WEIGHT

15690 lbs+ [7120] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR