
| UNIT   | CLOSED CIRCUIT COOLER |           |
|--------|-----------------------|-----------|
| MODEL# | ATWB 7-4J14           | SCALE NTS |

## EVAPCO, INC. Evapco


## **NOTES**


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]



**FACE C** 

**FACE D** 





FACE B FACE A

 
 SHIPPING WEIGHT
 12180 lbs+ [5525] kg+
 OPERATING WEIGHT
 16760 lbs+ [7605] kg+
 HEAVIEST SECTION WEIGHT
 9990 lbs+ [4535] kg+
 NO. OF SHIPPING SECTIONS
 2
 DRAWN BY:
 JLG