UNIT CLOSED CIRCUIT COOLER			EVAE	OCO TA	IC ev	apeo [®]	DWG. # WV030606-DRC-ST	REV.
MODEL # eco-	LRWB 3-3E6	^{SCALE} NTS	T EVAR	PCO, IN	VC.		SERIAL #	DATE 11/1/2025
FPT DENOTES BFW DENOTES GVD DENOTES FLG DENOTES PE DENOTES 3. +UNIT WEIGH' ACCESSORIES 4. 3/4" [19mm] DI. RECOMMENDI 5. DIMENSIONS I 6. * - APPROXIM/ USE FOR PRE 7. MAKE-UP WAT	S MALE PIPE THREAD IFEMALE PIPE THREAD IFEMALE PIPE THREAD IFEMALE PIPE THREAD IFEMALE	RAWINGS) REFER TO RAWING ENGLISH FT IN [METRIC] [mm IOT INECTING PIP	PLAN VIEW	3'-4 1/2" [1029]		FACE C 10'-1 7/8" [3096]		FACE D
-	1'-8 1/4" *					FACE A		
4" [100] BFW - FLUID IN 4" [100] BFW - FLUID OUT 3 1/4" TYP 2" [50] MPT - OVERFLOW 2" [50] MPT - DRAIN	3 7/8" [98] 3'-4 1/2" [1029] FACE B	2	6'-7 3/4" [2026] 5 1/4" * [133] * 3'-1/4" [919] 8 3/4" [222]	'-1 1/8" (333)	1/2" [15] FPT VENT ACCESS DOOR	5'-6" 1676] 10'-1 7/8" [3096] FACE A		=
SHIPPING WEIGHT	2820 lbs+ [1280] k	(g+	OPERATING 4150 lbs+	[1885] kg+	HEAVIEST SECTION WEIGHT	2820 lbs+ [1280] kg+	NO. OF SHIPPING SECTIONS 1	DRAWN BY: TLS