UNIT CLOSED CIRCUIT COOLER						apco	WG. # WV030608-DRC	:-ST	REV.
MODEL #	LRWB 3-4H6	SCALE NTS	† EVAI	PCO, II	VC.	S	ERIAL #		DATE 11/3/2025
2. MPT DEN FPT DENG BFW DENG GVD DEN FLG DENG PE DENO 3. +UNIT WE ACCESSO 4. 3/4" [19mr RECOMM 5. DIMENSIO 6. * - APPRO USE FOR 7. MAKE-UP	MOTOR LOCATION OTES MALE PIPE THRE OTES FEMALE PIPE THRE OTES GROOVED OTES GROOVED OTES FLANGE TES PLAIN END EIGHT DOES NOT INCLUDING ONE STEEL SUPPOR ONS LISTED AS FOLLOW OXIMATE DIMENSIONS DE PRE-FABRICATION OF WATER PRESSURE 7 KPa] MIN, 50 psi [344 kl	READ /ELDING JDE Y DRAWINGS) ES. REFER TO RT DRAWING VS: ENGLISH FT IN [METRIC] [mm] DO NOT CONNECTING PIPI	PLAN VIEW	3'-4 1/2"		FACE C 10'-1 7/8" _ [3096]			FACE D
	[514 j * -		+ +			FACE A]		
4" [100 FLi 4" [100] E	UID IN	2'-3" [686]	4'-3" [1297]		- 1/2" [15] FPT VENT			•	1
FLUID (3 1/4" TY [83]	OUT		7'-3 1/4" [2216] 5 1/4" *		ACCESS — DOOR		ACCESS DOOR		5'-3 3/8" [1610]
2" [50] OVERF 2" [50] DF	LOW		3'-1/4" [919] 8 3/4"						1'-8 1/8" [511]
· Di		7/8" 2 6	8 3/4" [222]	1'-1 1/8"		5'-6"	└─ 1" [25] MPT MAKE-UP	-	
SHIPPING WEIGHT	2870 lbs+ [13	05] kg+	OPERATING 4300 lbs-	+ [1955] kg+	HEAVIEST SECTION WEIGHT	2870 lbs+ [1305] kg+	NO. OF SHIPPING SECTIONS	1	DRAWN BY: TLS