



UNIT	CLOSED CIRCUIT COOLER			DWG. #	WV081212-DRE-SF	REV.
MODEL #	eco-LRWB 8-6N12-Z	SCALE NTS		SERIAL #		DATE 1/31/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
[METRIC] [mm]
6. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF
CONNECTING PIPING.
7. MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
8. SERIES FLOW PIPING AND AUX. CROSSOVER
DRAIN ARE BY OTHERS



DWG. #	WV081212-DRE-SF	REV.	-
SERIAL #		DATE	1/31/2026



SHIPPING WEIGHT 16740 lbs+ [7595] kg+ OPERATING WEIGHT 24650 lbs+ [11185] kg+ HEAVIEST SECTION WEIGHT 16740 lbs+ [7595] kg+ NO. OF SHIPPING SECTIONS 1 DRAWN BY: