UNIT CLOSED CIRCUIT COOLER	EVADOO TI	NC evapeo	DWG. # WV080910-DRD-ST	REV.
MODEL # LRWB 8-5M9 SCALE NTS	EVAPCO, II	NC.	SERIAL #	DATE 11/3/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT II [METRIC] [mm] 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIF 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX	n]	FACE O		FACE D
3" [80] MPT	1'-3 7/8 [405]	FACE A	<u> </u>	6'-7 3/4" [2026] ACCESS DOOR
SHIPPING 10010 lbs+ [4545] kg+ WEIGHT	OPERATING WEIGHT 15450 lbs+ [7010] kg+	HEAVIEST SECTION 10010 lbs+ [4545] kg+	NO. OF SHIPPING SECTIONS 1	RAWN BY: TLS