UNIT	CLOSED CIRCUIT COOLER			[®] DWG. # WV080908-DRE-SF		WV080908-DRE-SF	REV.	
MODEL #	LRWB 8-4M9-Z	SCALE NTS	EVAPCO, 1	INC.	evapco	SERIAL #		DATE 11/4/2025
2. MPT FPT BFW GVD FLG PE D 3. +UNI ACC' 4. 3/4" [REC' 5. DIME 6. * - AF USE CON 7. MAK 20 ps 8. SERI		AD READ ELDING JDE Y DRAWINGS) ES. REFER TO IT DRAWING VS: ENGLISH FT IN [METRIC] [mm] DO NOT	FACE B [7:-1] PLAN VIEW		FACE (<u>C</u>		FACE D
	2'-1/2" * - - 3'-6 [622] * - [1	8 7/8" * - 			FACE A			
(2) 4" [[100] BFW FLUID IN	(140)	·		(2) 1/2" [15] FPT VENT SERIES FLOW PIPING		6'-3" [1905]	-
F	[100] BFW FLUID OUT		2'-3"		(BY OTHERS) AUX. CROSSOVER DRAIN (BY OTHERS) ACCESS DOOR			6'-7 3/4" [2026]
3" [OV	[80] MPT ERFLOW [50] MPT DRAIN	4 1/4" [108] - 2'-10" [864] 2388] ACE B	2 5/8"	7/8"	8'-5 3/8" [2575] 15	4629]	1'-8 1/8" [511] ' [50] MPT AKE-UP	ACCESS DOOR

HEAVIEST SECTION WEIGHT

8650 lbs+ [3925] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

SHIPPING WEIGHT OPERATING WEIGHT

13700 lbs+ [6215] kg+

8650 lbs+ [3925] kg+