

UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. #	WLEP83612-DRD-ST	REV.
MODEL #	eco-LSWE 8P-6N36	SCALE NTS		SERIAL #	DATE	7/2/2025

NO

1. (M)- FAN MOTOR LOCATION
 2. HEAVIEST SECTION IS COIL SECTION
 3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
 4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
 5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
[METRIC] [mm]
 7. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING
 8. MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX



DWG, #


WLEP83612-DRD-ST

REV.

SFR1A1

DATE 7/2/2025

^G PLAN VIEW



SHIPPING WEIGHT 50650 lbs+ [22975] kg+ **OPERATING WEIGHT** 70650 lbs+ [32050] kg+ **HEAVIEST SECTION WEIGHT** 20300 lbs+ [9210] kg+ **NO. OF SHIPPING SECTIONS** 3 **DRAWN BY:** TLS