

UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-LSWE 10-3K18


**EVAPCO, INC.** 

DWG. #	WLETM1806-DRD-ST	REV.	-
SERIAL #		DATE	2/21/2026

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- MAKE-UP WATER PRESSURE  
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX


**FACE C**



**FACE D**

**FACE B**

**PLAN VIEW**



SHIPPING  
WEIGHT

21950 lbs+ [9960] kg+

OPERATING  
WEIGHT

31700 lbs+ [14380] kg+

HEAVIEST SECTION  
WEIGHT

14820 lbs+ [6725] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:  
TLS