INIT	CLOSED CIRCUIT COOLER	
IODEL #	eco-I SWF 4-316-7	SCALE NITS

EVAPCO, INC. Evapeo


DWG. # WLE040606-DRD-SF REV. SERIAL # DATE\_11/27/2025

**FACE D** 


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE
- ACCESSORIES (SEE ACCESSORY DRAWINGS)
  4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm] 6. \* APPROXIMATE DIMENSIONS DO NOT
- USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. HEAVIEST SECTION IS COIL SECTION
- 8. MAKE-UP WATER PRESSURE
- 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 9. MAKE-UP CONNECTION LOCATED 7-5/8" [194]
- FROM CONNECTION END OF UNIT
- 10. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS

## FACE C



**FACE A** 





SHIPPING WEIGHT 3200 lbs+ [1455] kg+

OPERATING WEIGHT

4250 lbs+ [1930] kg+

HEAVIEST SECTION WEIGHT

1990 lbs+ [905] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: