UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. Evapeo			® DW	/G. # WL	E041210-DRD-SF	REV	
MODEL #	eco-LSWE 4-5K12-Z	SCALE NTS	EVAPCO	, INC.		SEF	RIAL #		DATE <sub>11/27/2025</sub>
2. MPT FPT BFW GVD FLG PE D 3. +UNI ACC 4. 3/4" REC 5. DIME 6. * - AF USE 7. HEA' 8. MAK 20 px 9. MAK FRO 10. SEF	FAN MOTOR LOCATION DENOTES MALE PIPE THREADENOTES FEMALE PIPE THREADENOTES BEVELED FOR WIDENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END T WEIGHT DOES NOT INCLUITESSORIES (SEE ACCESSORY 19mm) DIA. MOUNTING HOLE DIAMMENDED STEEL SUPPORTINGIONS LISTED AS FOLLOW PPROXIMATE DIMENSIONS DIFOR PRE-FABRICATION OF COMEST SECTION IS COIL SECTION WATER PRESSURE EI [137 KPa] MIN, 50 psi [344 KPE-UP CONNECTION LOCATED CONNECTION LOCATED CONNECTION END OF UNITED SECTION FOR UNITED SECTION END OF UNITED SECTION END	EAD ELDING  DE / DRAWINGS) S. REFER TO T DRAWING 'S: ENGLISH FT II [METRIC] [mm O NOT CONNECTING PIF FION  Pa] MAX D 7-5/8" [194]	PLAN VIEW			11'-11 3/ [ 3651 ]	4"		FACE D
	1'-1/8" * [ 308 ] *  (2) 4" [100] BFW FLUID IN  SERIES FLOW PIPING (BY OTHERS)  (2) 4" [100] BFW FLUID OUT  (2) ACCESS DOOR  1" [25] MPT MAKE-UP  2'-2 1/8" [664]  1'-7 5/8" [498]  1'-8 7/8" [530]	4'-3/4" [1238] FACE	L'-8" *  2'-10 1/2" * [1549]  2" [50] FPT OVERFLOW  3'-7 1/2" [1105]  1'-6 7/8" [479]  2" [50] MPT DRAIN  1'-7" [483]	8'-8 1/2" [ 2654 ] 1'-5" [ 432 ]	(2) 1/2" [15] FPT VENT  AUX. CROSSOVER DRAIN (BY OTHERS)		4"		
SHIPPING WEIGHT	7790 lbs+ [353	85] kg+	OPERATING 10270 lbs+ [4660] kg+	HEAVIEST SI WEIGH	ECTION 5620 lbs-	+ [2550] kg+	NO. OF SHIPPIN	NG SECTIONS 2	DRAWN BY: TLS