

UNIT	CLOSED CIRCUIT COOLER
MODEL #	LSWE 10-3L18


**EVAPCO, INC.** 

DWG. #	WLETM1806-DRD-ST	REV.	-
SERIAL #		DATE	2/13/2026

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
8. MAKE-UP WATER PRESSURE  
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX

**FACE C**




**FACE D**

**PLAN VIEW**



**FACE A**



**FACE A**

**FACE B**

SHIPPING  
WEIGHT

18720 lbs+ [8495] kg+

OPERATING  
WEIGHT

28470 lbs+ [12915] kg+

HEAVIEST SECTION  
WEIGHT

11530 lbs+ [5230] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:  
TLS