JNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-I SWF 8P-4N12-7	SCALE NTS

EVAPCO, INC. Evapeo


DWG. # REV. WLEP81208-DRE-SF DATE_{11/26/2025} SERIAL #


FACE D


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. HEAVIEST SECTION IS COIL SECTION
- 8. MAKE-UP WATER PRESSURE
- 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 9. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS

FACE C







FACE A

FACE B

DRAWN BY: NO. OF SHIPPING SECTIONS **SHIPPING OPERATING** HEAVIEST SECTION 13660 lbs+ [6200] kg+ 19220 lbs+ [8720] kg+ 9630 lbs+ [4370] kg+ WEIGHT WEIGHT WEIGHT