UNIT	CLOSED CIRCUIT COOLER		EVADOO TE	NC evapeo	wg. # WV030610-DRC-ST	REV.
MODEL #	eco-LRWB 3-5G6	SCALE NTS	EVAPCO, I	NC.	SERIAL #	DATE _{11/26/2025}
2. MPT DI FPT DE BFW D GVD DI FLG DE PE DEI 3. +UNIT ' ACCES 4. 3/4" [19 RECOM 5. DIMEN 6. * - APP USE FC 7. MAKE-I	IN MOTOR LOCATION ENOTES MALE PIPE THRE ENOTES FEMALE PIPE THRE ENOTES BEVELED FOR W ENOTES GROOVED ENOTES PLAINE NOTES PLAIN END WEIGHT DOES NOT INCLU ESORIES (SEE ACCESSOR OMM) DIA. MOUNTING HOLI MMENDED STEEL SUPPOR SIONS LISTED AS FOLLOW ROXIMATE DIMENSIONS DE DR PRE-FABRICATION OF UP WATER PRESSURE 137 KPa] MIN, 50 psi [344 KF	READ FELDING JDE Y DRAWINGS) ES. REFER TO ET DRAWING VS: ENGLISH FT IN [METRIC] [mm] DO NOT CONNECTING PIPIN	FACE B 3'-4 1/2" PLAN VIEW	FACE C		FACE D
	1'-8 1/4" * -			10'-1 7/8' [3096] FACE A	-	
4" [10 FLU 3 1/4' [83] 2" [OV	<u></u>	7/8" 25 65 11	7'-10 3/4" [2407] 1/4" * 133] * 8 3/4" [222]	ACCESS DOOR 5'-6" [1676] 10'-1 7/8" [3096] FACE A		5'-3 3/8" [1610] 1'-8 1/8" [511]
SHIPPING WEIGHT	3740 lbs+ [170		PERATING 5280 lbs+ [2395] kg+ WEIGHT	HEAVIEST SECTION 3740 lbs+ [1700] kg+	NO. OF SHIPPING SECTIONS 1	DRAWN BY: TLS