UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-LSWE 8P-6N18-Z


EVAPCO, INC. Evapco

DWG. # REV. WLEP81812-DRD-SF DATE_{11/26/2025} SERIAL #


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC1 [mm]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. HEAVIEST SECTION IS COIL SECTION
- 8. MAKE-UP WATER PRESSURE
- 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 9. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS

FACE C



FACE A





FACE A

SHIPPING 25700 lbs+ [11660] kg+ WEIGHT

OPERATING WEIGHT

35650 lbs+ [16175] kg+

HEAVIEST SECTION WEIGHT

20300 lbs+ [9210] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

FACE D