UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-LRWB 8-6O12	SCALE NTS


EVAPCO, INC. Evapeo


DWG. # WV081212-DRD-ST REV. SERIAL # DATE 11/1/2025


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX

FACE C







SHIPPING WEIGHT 16750 lbs+ [7600] kg+

OPERATING WEIGHT

24660 lbs+ [11190] kg+

HEAVIEST SECTION WEIGHT

16750 lbs+ [7600] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: