| JNIT | CLOSED CIRCUIT COOLER | | EVAPCO, INC. EVEPPO SERIAL # WV030604-DRD-SF | | REV | |
|---|--|--|---|--|----------------|---|
| MODEL # | eco-LRWB 3-2E6-Z | SCALE NTS | EVAPCO, I | NC. | SERIAL # | DATE _{10/31/2025} |
| 2. MPT DI FPT DE BFW D GVD D FLG DE PE DE! 3. +UNIT ACCES 4. 3/4" [19 RECOM 5. DIMEN 6. * - APP USE FO CONNE 7. MAKE- 20 psi [8. SERIES | IN MOTOR LOCATION ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WE ENOTES GROOVED ENOTES PLAINE NOTES PLAIN END WEIGHT DOES NOT INCLUE ESORIES (SEE ACCESSORY OMM) DIA. MOUNTING HOLE: MENDED STEEL SUPPORT SIONS LISTED AS FOLLOWS ROXIMATE DIMENSIONS DO DR PRE-FABRICATION OF ECTING PIPING. UP WATER PRESSURE 137 kPa] MIN, 50 psi [344 kPa] S FLOW PIPING AND AUX. C ARE BY OTHERS | EAD ELDING DE DRAWINGS) S. REFER TO TORAWING S: ENGLISH FT IN [METRIC] [mm] D NOT | FACE B 3'-41/2" PLAN VIEW | FACE C | 8" | FACE D |
| (2) 4" [10 | oj BFW | 1'-6" * | 3'-7 1/2" | (2) 1/2" [15] FPT VENT SERIES FLOW PIPING | [1270] | - |
| 3 1/4" [83] ¹ 2" [OVI | 50] MPT ERFLOW | [305] | 6'-7 3/4" [2026] 1'-3/4" * [324] * | AUX. CROSSOVER DRAIN (BY OTHERS) ACCESS DOOR | ACCESS DOOR | 5'-3 3/8" [1610] 1'-8 1/8" [511] |
| SHIPPING WEIGHT | 37 7 19 19 19 19 19 19 19 19 19 19 19 19 19 | 8) - 6 | 8 3/4" [222] | [1676] 10'-1 7/ (3096 FACE A HEAVIEST SECTION WEIGHT 2420 lbs+ [1100] kg+ | | RAWN BY: |