| JNIT | CLOSED CIRCOIT COOLER | | EVAPCO, INC. EVAPCO SERIAL # WV030604-DRD-SF | | DWG. # WV030604-DRD-SF | REV. |
|---|---|--|---|---|----------------------------|---------------------------|
| MODEL # | eco-LRWB 3-2F6-Z | SCALE NTS | EVAPCO, I | NC. | SERIAL # | DATE 11/1/2025 |
| 2. MPT DE FPT DE BFW D GVD DI FLG DE PE DEN 3. +UNIT N ACCES 4. 3/4" [19 RECON 5. DIMEN: 6. * - APP USE FC CONNE 7. MAKE-I 20 psi 8. SERIES | N MOTOR LOCATION ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WE ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUE ESORIES (SEE ACCESSORY Imm] DIA. MOUNTING HOLE MENDED STEEL SUPPORT SIONS LISTED AS FOLLOWS ROXIMATE DIMENSIONS DO DR PRE-FABRICATION OF ECTING PIPING. UP WATER PRESSURE 137 kPa] MIN, 50 psi [344 kPa S FLOW PIPING AND AUX. C ARE BY OTHERS | EAD ELDING DE DRAWINGS) S. REFER TO TORAWING S: ENGLISH FT IN [METRIC] [mm] D NOT | FACE B 3'-41/2" PLAN VIEW | FACE C | | FACE D |
| 11 1/4 [286 | 4" * | 1'-6" * | | (2) 1/2" [15] FPT VENT | 4'-2" [1270] | |
| (2) 4" [1 | O] BFW UID IN OO] BFW UID OUT | 1'-0" | * 3'-7 1/2" 1106] | SERIES FLOW PIPING (BY OTHERS) | | |
| OVE | 50] MPT | | 6'-7 3/4" [2026] 1'-3/4" * [324] * 3'-1/4" [919] | AUX. CROSSOVER DRAIN (BY OTHERS) ACCESS DOOR | ACCESS DOOR | 5'-3 3/8" [1610] |
| | 3 7 [98] 3'-4 1/2" [1029] FACE B | 6 ⁰ 1 → → | 5/8" 1'-1 1/8" 5/8" 1'-1 1/8" 167] | 5'-6" [1676] 10'-1 7/ [3096 | | - |
| SHIPPING WEIGHT | 2450 lbs+ [1115 | 5] kg+ | PERATING 3680 lbs+ [1670] kg+ WEIGHT | HEAVIEST SECTION 2450 lbs+ [1115] kg+ | NO. OF SHIPPING SECTIONS 1 | RAWN BY: |