UNIT CLOSED CIRCUIT COOLER	EVADOO TI	NO EVOIDED	DWG. # WV030606-DRD-SF	REV.
MODEL # eco-LRWB 3-3E6-Z SCALE NTS	EVAPCO, I	NC.	SERIAL #	DATE 11/1/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm] 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING. 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 8. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS		FACE C 10'-1 7/8 [3096]		FACE D
11 1/4" * - 1'-6" * [457] *		PACE A		
(2) 4" [100] BFW FLUID IN (2) 4" [100] BFW FLUID OUT 3 1/4" TYP	3'-7 1/2" [1106] 1/2" * [5] * 6'-7 3/4" [2026] 3'-1/4" [919]	(2) 1/2" [15] FPT VENT SERIES FLOW PIPING (BY OTHERS) AUX. CROSSOVER DRAIN (BY OTHERS) ACCESS DOOR	4'-2" [1270] ACCESS DOOR	5'-3 3/8" [1610]
	2 5/8" [67] 6 5/8" [1-1 1/8" [333]	5'-6" [1676] 10'-1 7/8 [3096] FACE A	1" [25] MPT MAKE-UP	<u> </u>
FACE B		INCEA		
SHIPPING 2820 lbs+ [1280] kg+	OPERATING 4150 lbs+ [1885] kg+	HEAVIEST SECTION 2820 lbs+ [1280] kg+	NO. OF SHIPPING SECTIONS 1	RAWN BY: