UNIT CLOSED CIRCUIT COOLER			EVADO	O THE F	/dpco	WV030610-DRD-SF	REV.
MODEL #	eco-LRWB 3-5H6-Z	SCALE NTS	EVAPO	O, INC.	SE	RIAL #	DATE _{11/26/2025}
2. MPT DEI FPT DEN BFW DE GVD DE FLG DEN PE DEN 3. +UNIT W ACCESS 4. 3/4" [19n RECOMI 5. DIMENS	I MOTOR LOCATION NOTES MALE PIPE THREAD NOTES FEMALE PIPE THREAD NOTES BEVELED FOR WELF NOTES GROOVED NOTES FLANGE OTES PLAIN END JEIGHT DOES NOT INCLUDE GORIES (SEE ACCESSORY D nm] DIA. MOUNTING HOLES. MENDED STEEL SUPPORT D IONS LISTED AS FOLLOWS:	AD DING E RAWINGS) REFER TO DRAWING ENGLISH FT IN [METRIC] [mm]	FACE B 3'-4 1/2" [1029] PLAN VIEW		FACE C		FACE D
USE FOI CONNEC 7. MAKE-U 20 psi [1: 8. SERIES DRAIN A	R PRE-FABRICATION OF CTING PIPING. P WATER PRESSURE 37 kPa] MIN, 50 psi [344 kPa] FLOW PIPING AND AUX. CRI RE BY OTHERS	MAX OSSOVER			10'-1 7/8" [3096] <u>FACE A</u>		
(2) 4" [(2) 4" [FI 3 1/4" [83] 2" O\ 2"	100] BFW FLUID IN FLUID OUT (100) BFW LUID (100) BFW	ĭ -	7'-10 3/4" [2407] 5 1/4" * [133] * 3'-1/4" [919] 8 3/4" [222]	AUX. CROSS (BY OTHERS) ACCESS DOOR	SOVER DRAIN (5)	ACCESS DOOR 1" [25] MPT MAKE-UP	5'-3 3/8" [1610] 1'-8 1/8" [511]
SHIPPING WEIGHT	3790 lbs+ [1720]	kg+	OPERATING 5330 lbs+ [2420 WEIGHT	HEAVIEST SECTION WEIGHT	3790 lbs+ [1720] kg+	NO. OF SHIPPING SECTIONS 1	DRAWN BY:
			-				