UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 4-5F12	SCALE NTS

EVAPCO, INC. Evapeo

FACE B

PLAN VIEW



DWG. # REV. WB3041210-DRE-ST DATE_{12/15/2025} SERIAL #

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN METRIC [mm]



FACE C ACCESS DOOR ACCESS DOOR **FACE D** 4'-5 3/4 [1365]

FACE A

1'-10 1/2" * 4" [100] BFW 7'-2 7/8" [2207] FLUID IN 4" [100] BFW 10'-4 3/8" [3159] FLUID OUT 2'-10 1/2" * 1" [25] MPT MAKE-UP 2" [50] FPT OVERFLOW 3'-6 3/4" [1086] 1'-1" 1'-7 3/4" [330] 3" [76] 2" [50] MPT **FACE B**



DRAWN BY: NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 7920 lbs+ [3595] kg+ 11340 lbs+ [5145] kg+ 7100 lbs+ [3225] kg+ WEIGHT WEIGHT WEIGHT