



UNIT	CLOSED CIRCUIT COOLER			DWG. #	WV080910-DRE-SF	REV.
MODEL #	eco-LRWB 8-5L9-Z	SCALE NTS		SERIAL #		DATE 1/31/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD
3. BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED
4. FLG DENOTES FLANGE  
PE DENOTES PLAIN END
5. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING
7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN  
[METRIC] [mm]
6. \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF  
CONNECTING PIPING.
7. MAKE-UP WATER PRESSURE  
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
8. SERIES FLOW PIPING AND AUX. CROSSOVER  
DRAIN ARE BY OTHERS



SHIPPING WEIGHT 12110 lbs+ [5495] kg+ OPERATING WEIGHT 17550 lbs+ [7965] kg+ HEAVIEST SECTION WEIGHT 12110 lbs+ [5495] kg+ NO. OF SHIPPING SECTIONS 1 DRAWN BY: