

UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-LSWE 4-3H12


**EVAPCO, INC.** 

DWG. #	WLE041206-DRD-ST	REV.	-
SERIAL #		DATE	2/1/2026


NOTES:

- (M) - FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- MAKE-UP WATER PRESSURE  
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
- MAKE-UP CONNECTION LOCATED 7-5/8" [194] FROM CONNECTION END OF UNIT


**FACE C**



**FACE B**  
**PLAN VIEW**



**FACE D**



**FACE A**

**FACE B**

SHIPPING  
WEIGHT

5750 lbs+ [2610] kg+

OPERATING  
WEIGHT

7770 lbs+ [3525] kg+

HEAVIEST SECTION  
WEIGHT

3780 lbs+ [1715] kg+

NO. OF SHIPPING SECTIONS  
2

DRAWN BY:  
TLS