UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 9-4I11


EVAPCO, INC. Evapeo





DWG. # REV. WB3091108-DRC-ST DATE<sub>11/22/2025</sub> SERIAL #

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]







**SHIPPING** 12800 lbs+ [5810] kg+ WEIGHT

**OPERATING** WEIGHT

17970 lbs+ [8155] kg+

HEAVIEST SECTION WEIGHT

11160 lbs+ [5065] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR