UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-LSWE 10-3K18	SCALE NTS



DWG. # WLETM1806-DRD-ST REV. SERIAL # DATE\_11/26/2025

## NOTES:

**SHIPPING** 

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE
- ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TÓ RECOMMENDED STEEL SUPPORT DRAWING
- 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 7. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

**FACE B** 


21950 lbs+ [9960] kg+

**OPERATING** 

WEIGHT

8. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX


## **FACE C**



FACE D

DRAWN BY:

NO. OF SHIPPING SECTIONS



31700 lbs+ [14380] kg+

HEAVIEST SECTION

WEIGHT

14820 lbs+ [6725] kg+