NIT	CLOSED CIRCUIT COOLER		EVA DCO	TNG	DWG. # WLE040906-DRD	O-SF REV
ODEL #	eco-LSWE 4-3H9-Z	SCALE NTS	EVAPCO,	INC. evapco	SERIAL #	DATE _{11/27/2025}
2. MPT L FPT D BFW I GVD L FLG D PE DE 3. +UNIT ACCE 4. 3/4" [1 RECO 5. DIMEN 6. * - API USE F 7. HEAV 8. MAKE 20 ppi 9. MAKE FROM 10. SERI	AN MOTOR LOCATION DENOTES MALE PIPE THRE JENOTES FEMALE PIPE THE DENOTES BEVELED FOR W DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END WEIGHT DOES NOT INCLUS SSORIES (SEE ACCESSOR SOMMED TO STEEL SUPPON MEIGHT DOES NOT INCLUS SORIES (SEE ACCESSOR SOMMED STEEL SUPPON SIONS LISTED AS FOLLOW PROXIMATE DIMENSIONS INCOME PRE-FABRICATION OF JEST SECTION IS COIL SEC L'UP WATER PRESSURE [137 kPa] MIN, 50 psi [344 k- L'UP CONNECTION LOCATE I CONNECTION END OF UN JES FLOW PIPING AND AUX NARE BY OTHERS	UDE RY DRAWINGS) LES. REFER TO RT DRAWING WS: ENGLISH FT IN [METRIC] [mm] DO NOT F CONNECTING PIPING CTION KPA] MAX ED 7-5/8" [194]	FACE B PLAN VIEW		1 1/4"	FACE D
	1'-1/8" * - [308] * - [308] * - (2) 4" [100] BFW — FLUID IN SERIES FLOW — PIPING (BY OTHERS) (2) 4" [100] BFW — FLUID OUT (2) ACCESS DOOR — 1" [25] MPT — MAKE-UP 2'-2 1/8" [664] 1'-7 5/8" — [498] — 1'-8 7/8" [530]	4'-3/4"	1'-8" * 1'-7 1/2" * [496] * 2" [50] FPT	(2) 1/2" [15] FPT VENT AUX. CROSSOVER DRAIN (BY OTHERS) 1'-2" [356] 8'-11: [272 FACE A		
SHIPPING WEIGHT	4390 lbs+ [19	P95] kg+ OPERAT WEIG	TING 5070 lbc [2710] kg	HEAVIEST SECTION 2850 lbs+ [1295] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY: TLS