



UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3171212-DRD-ST	REV. -
MODEL # eco-ATWB 17-6L12	SCALE NTS		SERIAL #	DATE 9/13/2025

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE C




(2) ACCESS DOOR

FACE B

PLAN VIEW


FACE D

FACE A



(4) 1/2" [15] FPT VENT


FACE B



Dimensions for FACE B (Front View):

- Top width: 1'-9 3/8" [543]
- Top width: 4'-3/4" [1238]
- Top width: 2'-2 3/8" [670] *
- Height: 8'-10" [2694]
- Height: 13'-10 1/4" [4223]
- Height: 3'-6" [1067] *
- Height: 6" [154] *
- Height: 5'-1/4" [1529]
- Height: 1'-11 1/8" [589]
- Height: 3" [76]
- Height: 1'-3 5/8" [397]
- Height: 1'-3" [383]
- Height: 2'-10 1/4" [870]
- Height: 8'-1/4" [2445]
- Height: 8'-1 1/4" [2470]
- Height: 8'-5 1/2" [2578]
- Height: 5 1/8" [130]
- Height: 17'-4 1/8" [5286]
- Width: 1'-11 1/8" [589]
- Width: 3" [76]
- Width: 2" [50] MPT MAKE-UP
- Width: 2" [50] MPT DRAIN
- Width: 3" [80] MPT OVERFLOW
- Width: 4" [100] BFW FLUID IN
- Width: 4" [100] BFW FLUID OUT

FACE A



Dimensions for FACE A (Side View):

- Top width: 1'-7/8" [327]
- Height: 1'-3 5/8" [397]
- Width: 11'-11 3/4" [3651]