NIT	CLOSED CIRCUIT COOLER		EVA DCO		DWG. # WLE040906-DR	RD-SF REV
ODEL #	eco-LSWE 4-3J9-Z	SCALE NTS	EVAPCO,	INC. evapeo	SERIAL #	DATE _{11/27/2025}
2. MPT I FPT D BFW I GVD I FLG D PE DE 3. +UNIT ACCE 4. 3/4" [1 RECC 5. DIMEI 6. * - API USE F 7. HEAV 8. MAKE 20 psi FROM 10. SERI	AN MOTOR LOCATION DENOTES MALE PIPE THRE ENOTES FEMALE PIPE THRE DENOTES BEVELED FOR W DENOTES GROOVED ENOTES PLAIN END WEIGHT DOES NOT INCLUS SSORIES (SEE ACCESSOR 9mm] DIA. MOUNTING HOL MMENDED STEEL SUPPOR NSIONS LISTED AS FOLLOW PROXIMATE DIMENSIONS INTERPRESSURE (137 KPa] MIN, 50 psi [344 K-UP CONNECTION END OF UN ES FLOW PIPING AND AUX I ARE BY OTHERS	READ VELDING UDE RY DRAWINGS) LES. REFER TO RT DRAWING WS: ENGLISH FT IN [METRIC] [mm] DO NOT CONNECTING PIPING CTION EPA] MAX ED 7-5/8" [194]	FACE B PLAN VIEW		-11 1/4" 2724]	FACE D
	1'-1/8" *— [308] *— [308] *— (2) 4" [100] BFW————————————————————————————————————		1'-8" * 1'-7 1/2" * [496] * 2" [50] FPT OVERFLOW 3'-7" * [1168] 2" [50] FPT [178] * [1105] 1'-6 7/8" [479] 2" [50] MPT DRAIN 1'-3" [381]	(2) 1/2" [15] FPT VENT AUX. CROSSOVER DRAIN (BY OTHERS) 1'-2" [356] 8'-1: [2: FACE	1 1/4" 724]	
SHIPPING WEIGHT	4530 lbs+ [20	Longo	TING 6110 lbc [2775] kg	HEAVIEST SECTION 2850 lbs+ [1295] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY: TLS