UNIT CLOSED CIRCUIT COOLER			EVAPCO, INC. Evapeo				DWG. # WLE041206-DRD-SF			REV.
IODEL #	eco-LSWE 4-3K12-Z	SCALE NTS	T EVAPCO), INC.			SERIAL #			DATE _{11/27/2025}
2. MPT I FPT I BFW GVD I FLG I PE DI 3. +UNIT ACCE 4. 3/4" [' RECC 5. DIMEI 6. * - AP USE I 7. HEAV 8. MAKE 20 psis 9. MAKE FROM 10. SER	FAN MOTOR LOCATION DENOTES MALE PIPE THRE DENOTES FEMALE PIPE TH DENOTES BEVELED FOR V DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END T WEIGHT DOES NOT INCLE ESSORIES (SEE ACCESSOF 19mm] DIA. MOUNTING HOLE DIMMENDED STEEL SUPPO NSIONS LISTED AS FOLLO PROXIMATE DIMENSIONS FOR PRE-FABRICATION OF VIEST SECTION IS COIL SEC E-UP WATER PRESSURE IS [137 KPa] MIN, 50 psi [344 KE-UP CONNECTION LOCATE MICONNECTION END OF UN SIESS FLOW PIPING AND AUX N ARE BY OTHERS	UDE RY DRAWINGS) LES. REFER TO RT DRAWING WS: ENGLISH FT [METRIC] [mi DO NOT CONNECTING PI CTION (Pa] MAX ED 7-5/8" [194]	m] PI AN VTFW			FACE	['-11 3/4" —			FACE D
SE (E	1'-1/8" * [308] * [308		1'-8" * 1'-7 1/2" * 3'-10" [1168] 2" [50] FPT OVERFLOW 1'-6 7/8" [479]	7'-51/2" [2273]	(2) 1/2" [15] FPT VENT AUX. CROS DRAIN (BY	SOVER				
	1'-7 5/8" —— [498] 1'-8 7/8" —— [530]	4'-3/4" — [1238]	3 1/8" [79] 2" [50] MPT DRAIN 1'-7" [483]	1'-5" 432]	-	1 FACE .	1'-11 3/4" [3651] <u>A</u>			
SHIPPING WEIGHT	5950 lbs+ [27	700] kg+	OPERATING 7970 lbs+ [3620] kg-	HEAVIEST S WEIGI	ECTION 1T	3780 lbs+ [1715] kg+	NO. OI	F SHIPPING SECTIONS	2	DRAWN BY: TLS