EVAPCO, INC. Evapeo

DWG. # WLEP81206-DRD-SF REV. SERIAL # DATE_11/27/2025

FACE D

DRAWN BY:

NO. OF SHIPPING SECTIONS


NOTES:

SHIPPING


WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TÓ RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. HEAVIEST SECTION IS COIL SECTION
- 8. MAKE-UP WATER PRESSURE
- 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
- 9. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS

FACE C



7610 lbs+ [3455] kg+



16470 lbs+ [7475] kg+

HEAVIEST SECTION

WEIGHT

OPERATING

WEIGHT

11430 lbs+ [5185] kg+