
EVAPCO, INC. EVAPCO

DWG. # WLEP81810-DRD-SF REV. SERIAL # DATE 11/26/2025


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TÓ RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm] 6. * APPROXIMATE DIMENSIONS DO NOT
- USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. HEAVIEST SECTION IS COIL SECTION
- 8. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
- 9. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS

FACE C



FACE A



OPERATING WEIGHT

31790 lbs+ [14420] kg+

HEAVIEST SECTION WEIGHT

17230 lbs+ [7820] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

FACE D