INIT CLOSED CIRCUIT COOLER			EVAPCO, INC. Evapeo					DWG.	DWG. # WLETM1806-DRD-SF		
ODEL #	eco-LSWE 10-3L18-Z	SCALE NTS	E	VAPCO,	TI	C.		SERIA	L #		DATE 11/1/2025
2. MPT FPT BFW GVD FLG PE D 3. +UNI ACC: 4. 3/4" [REC: 5. DIME 6. * - AF USE 7. HEA' 8. MAK 20 ps 9. SERI	FAN MOTOR LOCATION DENOTES MALE PIPE THRE DENOTES FEMALE PIPE TH DENOTES BEVELED FOR W DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END T WEIGHT DOES NOT INCLUSESORIES (SEE ACCESSOR 19mm] DIA. MOUNTING HOLD MMENDED STEEL SUPPOR NSIONS LISTED AS FOLLOW PROXIMATE DIMENSIONS I FOR PRE-FABRICATION OF //IEST SECTION IS COIL SEC E-UP WATER PRESSURE i [137 kPa] MIN, 50 psi [344 k ES FLOW PIPING AND AUX. N ARE BY OTHERS	READ VELDING UDE RY DRAWINGS) LES. REFER TO RT DRAWING WS: ENGLISH FT IN [METRIC] [mm] DO NOT CONNECTING PIPIN CTION (Pa] MAX	NG	FACE B PLAN VIEW	. [2331]			FACE C			FACE D
	2'-6 3/8" * [772] SERIES FLOW PIPING (BY OTHERS)		[14	-9" * 448] * (4) 4" [100] BFW FLUID IN	T		(4) 1/2" [15] FPT VENT	18'-1/4' [5493] FACE A			
1'-10 [56: 4 3 [12	<u>*</u>	0		4'- (4) 4" [100] BFW [] FLUID OUT	-1 1/8" 1248] 	5/8"	AUX. CROSSOVER DRAIN (BY OTHERS)				
	3" [80] FPT OVERFLOW 2'-7 1/2" [800]			2" [50] MPT 8'- MAKE-UP 8'-	-6 1/2" 2604]					Y) 1	
	2'-7 3/4"		3" [80] MPT DRAIN	3 5/8" [92]		2'-1" [635]	•	18'-1/4' [5493] FACE A]		
SHIPPING WEIGHT	22010 lbs+ [99	FACE 0PI	B ERATING VEIGHT	31760 lbs+ [14410] kg+	HEA	VIEST SECTION WEIGHT	14820 lbs+ [6725] k	Ka+ N	IO. OF SHIPPING SECTIONS	2	DRAWN BY: TLS