UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 4-5G12	SCALE NTS

EVAPCO, INC. Evapeo



DWG. # REV. WB3041210-DRE-ST DATE_{12/14/2025} SERIAL #


FACE D

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN METRIC [mm]





FACE A





DRAWN BY: CAF NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 7940 lbs+ [3605] kg+ 11360 lbs+ [5155] kg+ 7120 lbs+ [3230] kg+ WEIGHT WEIGHT WEIGHT