



UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. #	WB3242810-DRC-ST	REV.
MODEL #	eco-ATWB 24-5M28	SCALE NTS		SERIAL #		DATE 2/8/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



FACE B



[0000]

SHIPPING WEIGHT 106800 lbs+ [48445] kg+ OPERATING WEIGHT 154860 lbs+ [70245] kg+ HEAVIEST SECTION WEIGHT 23590 lbs+ [10705] kg+ NO. OF SHIPPING SECTIONS 6 DRAWN BY: SLR