

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-4M40	SCALE NTS

# EVAPCO, INC.


DWG. #	WB3124008-DRC-ST	REV.	-
SERIAL #		DATE	2/19/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -\*APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING  
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN  
METRIC [mm]

## FACE B PLAN VIEW



SHIPPING WEIGHT 64320 lbs+ [29180] kg+ OPERATING WEIGHT 96000 lbs+ [43545] kg+ HEAVIEST SECTION WEIGHT 27650 lbs+ [12545] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: SLR