UNIT CLOSED CIRCUIT COOLER


MODEL # eco-ATWB 20-3M24 SCALE NTS


EVAPCO, INC. Evapco


DWG. # WB36M2406-DRC-ST REV.
SERIAL # DATE 11/18/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]







SHIPPING WEIGHT 60060 lbs+ [27245] kg+

OPERATING WEIGHT

90080 lbs+ [40860] kg+

HEAVIEST SECTION WEIGHT

12310 lbs+ [5585] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR