



| | | | | | | |
|---------|-----------------------|-----------|---|----------|------------------|----------------|
| UNIT | CLOSED CIRCUIT COOLER | | EVAPCO, INC.  | DWG. # | WB36M2406-DRC-ST | REV. |
| MODEL # | eco-ATWB 20-3M24 | SCALE NTS | | SERIAL # | | DATE 2/13/2026 |

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



FACE B
PLAN VIEW



FACE B



[7500]

SHIPPING WEIGHT 60060 lbs+ [27245] kg+ OPERATING WEIGHT 90080 lbs+ [40860] kg+ HEAVIEST SECTION WEIGHT 12310 lbs+ [5585] kg+ NO. OF SHIPPING SECTIONS 6 DRAWN BY: SLR