UNIT CLOSED CIRCUIT COOLER

MODEL # eco-ATWB 24-6M24 SCALE NTS





DWG. # WB3242412-DRD-ST REV. SERIAL # DATE\_11/21/2025


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]

## **FACE C**







SHIPPING WEIGHT 106420 lbs+ [48275] kg+ OPERATING WEIGHT 150680 lbs+ [68350] kg+ HEAVIEST SECTION WEIGHT 23810 lbs+ [10805] kg+ NO. OF SHIPPING SECTIONS 6 DRAWN BY: SLR